

## QUICK LOCK™ FITTINGS

For more info visit our website [www.tempoinc.com](http://www.tempoinc.com)

### Features:

- Extremely secure fit between tubing and fittings.
- Easy to assemble and can be disassembled for reuse.
- Locking nut can be released to remove tubing.
- Wide range of fittings available.
- Manufactured from talc filled polypropylene.
- Couplings have ergonomic center flange to hold fitting comfortably when connecting to tubing.
- Nominal size of fitting engraved on nut.
- Fittings can be used with 18 mm, 20 mm, 3/4" and 1" poly tubing.
- Made in USA.



## Quick Lock™ Fittings Selection Chart

Series	Tubing Nominal Size	Inside Diameter Range	Wall Thickness Range
600	0.600" ID x 0.700" OD (18 mm)	0.590" to 0.630" (15.0 mm to 16.0 mm)	0.040" to 0.050" (1.02 mm to 1.27 mm)
700	0.720" ID x 0.820" OD (20 mm)	0.700" to 0.740" (17.8 mm to 18.8 mm)	0.045" to 0.055" (1.14 mm to 1.40 mm)
800	0.820" ID x 0.940" OD (3/4")	0.800" to 0.840" (20.3 mm to 21.3 mm)	0.055" to 0.065" (1.40 mm to 1.65 mm)
1000	1.060" ID x 1.200" OD (1")	1.035" to 1.085" (26.3 mm to 27.6 mm)	0.065" to 0.075" (1.65 mm to 1.90 mm)